### Xcelera-CL+ PX8 Dual

PCI Express x8 Frame Grabber



#### **Key Features**

- · Half-length PCI Express x8 Board
- Acquires images from two Base or one Medium Camera Link cameras
- Rapid image acquisition and transfer rates beyond 1GB/s
- Supports Camera Link operations up to 85MHz
- Windows® XP and Windows 7 (32/64-bit) compatible
- · ROHS compliant
- On-board FPGA based real-time Bayer decoding and shading correction
- Power Over Camera Link (PoCL)
   Compliant
- Teledyne DALSA Platform Development Advantage – Free Run-time Licensing¹

## Advanced PCIe x8 image acquisition

Building on the field proven technology and performance of Teledyne DALSA's X64 frame grabbers the new X64 Xcelera Series leverages the PCI Express (PCIe) platform to bring traditional image acquisition and processing technology to new levels of performance and flexibility.

The PCIe host interface is a point-to-point host interface allowing simultaneous image acquisition and transfer without loading the system bus and involving little intervention from the host CPU. Designed with the requirements of the machine vision OEMs in mind, the Xcelera Series will range from entry level frame grabbers, to high-performance image acquisition boards, to embedded vision processors.

Addressing the emerging needs of bandwidth-hungry machine vision applications, Teledyne DALSA's Xcelera Series is defining next generation frame grabber capabilities with the ability to deliver bandwidth beyond 1GByte/s over multiple-lane PCI Express implementations with room to grow.

The X64 Xcelera-CL+ PX8 Dual is a Camera Link frame grabber that is based on the PCI Express x8 interface. Compatible with two Base or one Medium Camera Link cameras, the Xcelera-CL+ PX8 Dual supports a wide variety of multi-tap area and line scan colour and monochrome cameras.

The X64 Xcelera-CL+ PX8 Dual has been built within Teledyne DALSA's Trigger-to-Image Reliability technology framework. Trigger-to-Image Reliability leverages Teledyne DALSA's hardware and software innovations to control, monitor and correct the image acquisition process from the time that an external trigger event occurs to the moment the data is sent to the host, providing traceability when errors do occur and permitting recovery from those errors.

#### **Software Support**

All of the frame grabbers in the Xcelera series are supported by Teledyne DALSA's Sapera Vision Software packages:

Sapera Essential, the core development platform, includes over 400 image processing primitive and industrial strength image analysis tools such as pattern finding, 1D and 2D barcode and OCR tools for part identification and detection, color processing tool, separation and measurement applications, blob analysis tool and inspection metrology tool for real-world dimensional measurements.

#### Teledyne DALSA Platform Development Advantage - Free Run-Time Licensing

The Sapera Essential standard processing tool run-time license is offered at no additional charge when combined with the Teledyne DALSA frame grabbers. This software run-time license' includes access to image processing functions, area-based (normalized correlation based) template matching tool, blob analysis and lens correction tool.

Sapera Nitrous accelerates Sapera Essential applications by providing a seamless support for graphical processing units (GPU) and multi-core CPUs optimization (MCO).

Sapera Architect Plus gives system integrators and industrial vision automation specialists a userfriendly, non-programming graphical environment to quickly prototype and test drive application specific imaging tools within Sapera Essential and Sapera Nitrous.

<sup>1</sup>Some conditions and limitations apply, contact Teledyne DALSA sales for details.





# X64 Xcelera-CL+ PX8 Dual PCI Express x8 Frame Grabber

Function	Description	Function	Description
Board	Camera Link Specifications Rev 1.2 compatible	Controls	Comprehensive event notification includes
	Half length PCI Express 1.1 x8 compliant ROHS Compliant		start/end of frame/transfer events  Camera control signals for external event
Acquisition  Resolution	Supports two Base or one Medium Camera Link		synchronization
	area and line scan cameras		Optically isolated trigger inputs programmable as
	Acquisition pixel clock rates from 20MHz to 85MHz Horizontal Size (min/max): 16 byte/256K bytes		active high or low (edge or level trigger)
nesolution	Vertical Size (min/max):		TTL Strobes outputs
	1 line/infinite lines for line-scan cameras		PC independent serial communications ports
D. 15	1 line/16million lines/frame for area-scan cameras		provide support 9600 to 11500K baud  Appear as system serial ports enabling seamless
	Variable length frame size from 1 to 16 million lines for area-scan cameras		interface to host applications
	256MB onboard frame buffer memory	Encoder Inputs	Web synchronization using TTL/RS422 compatible
	Integrated advanced tap reversal engine allows		quadrature (AB) encoder Optically isolated input up to 200KHz
	independent tap formatting		RS422 input up to 5MHz
Pixel Format and Tap configuration	Supports Camera Link tap configurations for 8, 10,	On-board GPI/Os <sup>2</sup>	4-optically general purpose inputs tolerate 5 and
	12, 14 or 16-bit mono and 8, 10 or 12-bit RGB		24VDC signals 4 general purpose outputs
	For Base cameras in any of the following	Power Output	PoCL Compliant (4W max)
	combinations: 3x8-bit/tap, 2x10-bits/tap, 2x12-bit/tap,	Software	Power-on-reset fused +12V output @ 1.5A
	1x14-bit/tap, 1x16-bits/tap, & 1x24-bit/RGB		+5V DC output at 1.5A
	For Medium camera - 4x8-bit/tap, 4x10-bits/tap,		Device driver supports: Micrsoft Windows XP and Windows 7
	4x12-bit/tap, 1x30-bit/RGB, & 1x36-bits/tap		(32/64-bit) compatible
Transfers	B 18 1 1 1 1 1		Full support for Teledyne DALSA's Sapera Vision Software packages
	Real-time transfers to system memory Intelligent Data-Transfer-Engine automatically loads		Application development using C++ and .Net
	scatter-gather and tap description tables from the		languages(C++, C# or Visual Basic)
	host memory without CPU intervention	System Requirements	PCI Express Rev 1.1 compliant with one x8 slot
On-board Processing		Dimensions	system with 1024MB or higher system memory
Bayer Mosaic Filter	Hardware Bayer Engine supports two CameraLink Base or one Medium 8, 10 or 12-bit Bayer cameras	Temperature	6.375" (16.1cm) Length X 4.20" (10.7 cm) Height 10°C (50° F) to 50° C (122° F)
	Bayer output format supports 8 or 10-bit RGB/pixel	Tomporataro	Relative Humidity: up to 90% (non-condensing)
	Zero host CPU utilization for Bayer conversion	Markings	FCC Class B—Approved
Shading Correction	On the fly Flat-line and Flat-field correction with dead-pixel replacement		CE—Approved
	Supports two CameraLink Base or one Medium cameras		
	User programmable calibration gain/offset maps		
Output Lookup Tables	Fach input port has one OFC O 5th 4004 40 15	<sup>2</sup> Requires a separate slot	for the bracket assembly
Monochrome	Each input port has one 256x8-bit, 1024x10-bit, 4096x12-bit OLUTs		
Colour	Each input port has one 8-bit in/out, 10-bit in 10-bit		
	out, 12-bit in, 12-bit out Lookup table		

#### www.teledynedalsa.com

Americas Europe Asia Pacific Boston, USA Munich, Germany Tokyo, Japan +1 978-670-2000 +49 8142-46770 +81 3-5960-6353

sales.americas@teledynedalsa.com sales.europe@teledynedalsa.com sales.asia@teledynedalsa.com



Shanghai, China

+86 21-3368-0027

sales.asia@teledynedalsa.com